

**Termopar con aislamiento mineral IEC con sello de olla liso y 1 m de cable IEC con aislamiento de PFA - Tipo N - 1,5 mm x 150 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Necesita calibrar su sensor de temperatura?**

Trazable a ISO17025 estándares de calibración (UKAS), Labfacility ofrece una opción de calibración trazable de 3 o 5 puntos utilizando nuestra instalación de calibración interna.

**Tenga en cuenta que si agrega una opción de calibración a su pedido, se comunicará con usted con respecto a la información de entrega.**

**Características técnicas****Specifications**

|                             |                                                                                                        |
|-----------------------------|--------------------------------------------------------------------------------------------------------|
| <b>Product Code</b>         | XE-3165-001                                                                                            |
| <b>General Description</b>  | Plain pot seal (200°C) with 1 Metre of PFA insulated lead, 7/0.2mm flat pair with tails.               |
| <b>Sensor Type</b>          | Mineral Insulated                                                                                      |
| <b>Thermocouple Type</b>    | N                                                                                                      |
| <b>Element/hot junction</b> | Single element, junction insulated from sheath (offers protection against spurious electrical signals) |
| <b>Probe Diameter</b>       | 1.5mm                                                                                                  |
| <b>Probe Length</b>         | 150mm                                                                                                  |
| <b>Sheath Material</b>      | Nicrosil                                                                                               |
| <b>Pot Type</b>             | Plain (+200°C)                                                                                         |
| <b>Cable Length</b>         | 1M                                                                                                     |
| <b>Cable Type</b>           | PFA Teflon® insulated flat pair cable and tails (colour coded to IEC 584)                              |
| <b>Core / Strands</b>       | 7/0.2mm                                                                                                |
| <b>Termination Type</b>     | Bare Tails                                                                                             |

|                  |         |
|------------------|---------|
| Max. Temperature | 1300°C  |
| Min. Temperature | -100°C  |
| Tolerance        | Class 1 |
| Standards Met    | IEC 584 |