



Detectores de película plana de 500 ohmios - Clase B - 2 mm x 5 mm



Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.

All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.



Actualmente, Labfacility es un detector de película plana de múltiples fuentes para garantizar que podamos mantener un servicio de suministro a nuestros clientes sin afectar la calidad o la funcionalidad en el futuro previsible.

Todos los detectores de película plana suministrados, aunque difieren en apariencia y empaque en algunos casos, cumplirán con las especificaciones publicadas en nuestras hojas de datos.

Características técnicas

Specifications

Product Code	XE-4600-001
Element/hot junction	Thin film construction
Element	Pt500 to IEC751
Max. Temperature	500°C
Min. Temperature	-50°C
Tolerance	Class A in accordance with IEC 60751
Dimensions	2mm Width x 5mm Length
Important Information	Resists vibration & shock