



Detectores de película plana de 500 ohmios - Clase B - 2mm x 10mm



Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.

All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Labfacility est actualmente haciendo mltiples fuentes de detectores de pelcula plana para garantizar que podamos mantener un servicio de suministro a nuestros clientes sin afectar la calidad o funcionalidad en un futuro previsible.

Todos los detectores de pelcula plana suministrados, aunque en algunos casos difieran en apariencia y embalaje, cumplirn con las especificaciones publicadas en nuestras hojas tcnicas.

Especificaciones

Specifications

Product Code	XE-4603-001
Element/hot junction	Thin film construction
Element	Pt500 to IEC751
Max. Temperature	500°C
Min. Temperature	-50°C
Tolerance	Class A in accordance with IEC 60751
Dimensions	2mm Width x 10mm Length
Important Information	Resists vibration & shock