


## Detectores de película plana de 500 ohmios



**Labfacility are currently multi-sourcing flat film detectors in order to ensure we can maintain a supply service to our customers without affecting the quality or functionality for the foreseeable future.**

**All flat film detectors supplied, although differing in appearance and packaging in some cases, will meet the specifications as published on our data sheets.**

[Click here to view product](#)

Product Code	XE-4600
Element/hot junction	Thin film construction
Element	Pt500 to IEC751
Max. Temperature	+500°C
Min. Temperature	-50°C
Tolerance	Class B or A available in accordance with IEC 60751
Features #1	Resists vibration & shock