

Termmetro digital de horno DOT



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

TENGA EN CUENTA: El plazo de entrega ser de 7 a 10 das laborables al elegir la calibracin

Lectura de temperatura en solo 5 segundos

Suministrado completo con sonda de penetracin

Gran pantalla LCD

Alarma de temperatura audible fuerte de 70 dB

El Termmetro Digital de Horno DOT es un termmetro de cocina fcil de usar que muestra tanto la temperatura actual como la alarma audible. Simplemente ajusta la temperatura deseada usando los botones, inserta la sonda en tu comida, el DOT pitar y la pantalla parpadear cuando se alcance la temperatura.

El DOT incorpora una gran pantalla LCD y una alarma audible alta de 70 dB, lo que lo hace ideal para su uso en cocinas profesionales y concurridas.

Alojado en una caja resistente al agua y duradera, el DOT est diseado para colocarse sobre una encimera usando el soporte plegable, o para fijarse a un aparato mediante las almohadillas magnticas en la parte trasera del instrumento.

Cada unidad se suministra con una sonda de penetracin de 114 mm con un cable trenzado de acero inoxidable de 1,2 metros. Consulta a continuacin la especificacin completa.

Rango: -50 a 300C

Resolucin: 1 C/F

Precisin: 1C (-20 a 120 C)

Batera: 2 x AAA de 1,5 voltios

Duracin de la batera: 5000 horas

Volumen de alarma: 70dB

Tipo de sensor: termistor

Pantalla: LCD personalizada

Dimensiones: 20 x 80mm

Peso: 95 gramos

Material de la caja: plstico ABS

Garanta: un ao

Resistencia al agua y al polvo: proteccin IP65

Escala de medicin: Celsius/Fahrenheit

Specifications

Product Code	XE-3938-001
General Description	DOT Digital Oven Thermometer
Sensor Type	thermistor
Battery	2 x 1.5 volt AAA
Housing	ABS plastic
Display	LCD
Resolution	1 °C/°F
Max. Temperature	+120°C
Min. Temperature	-20°C
IP Rating	IP65
Accuracy	±1°C (-20 to 120 °C)
Dimensions	20 x 80mm
Weight	95 grams
Alarm volume	70dB
Features #1	Guarantee: one year
Features #2	supplied with a 114 mm penetration probe with a 1.2 metre stainless steel braided lead
Important Information	Please note that certificates supplied do not display an expiry date. They state the date the item was manufactured. The frequency of recalibration is determined by each customer's specific application requirements and internal quality procedures.