


**Termopar de unin expuesta IEC Doble trenzado  
con aislamiento PFA con tapn moldeado - Tipo K  
- 1/0,3 mm - 3 m de longitud**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

El tapn moldeado proporciona una construccin robusta y una terminacin impermeable.

### **Necesita calibrar su sensor de temperatura?**

Trazable a los estndares de calibracin ISO17025 (UKAS), Labfacility ofrece la opcin de una calibracin trazable de 3 o 5 puntos utilizando nuestra instalacin de calibracin interna, puede seleccionar cualquier punto de temperatura entre -10 C y +200 C.

**Tenga en cuenta que si agrega una opcin de calibracin a su pedido, nos pondremos en contacto con usted con respecto a la informacin de entrega**

### **Caractersticas tcnicas**

## **Specifications**

|                            |                                                                                                                 |
|----------------------------|-----------------------------------------------------------------------------------------------------------------|
| <b>Product Code</b>        | XE-0021-001                                                                                                     |
| <b>General Description</b> | Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc. |
| <b>Sensor Type</b>         | Exposed Junction                                                                                                |
| <b>Thermocouple Type</b>   | K                                                                                                               |
| <b>Cable Length</b>        | 3M                                                                                                              |
| <b>Cable Type</b>          | PFA insulated conductors twisted together                                                                       |
| <b>Core / Strands</b>      | 1/0.315mm                                                                                                       |
| <b>Termination Type</b>    | Miniature moulded flat pin plug, colour coded 'green' in accordance IEC specification                           |
| <b>Max. Temperature</b>    | 250°C                                                                                                           |
| <b>Min. Temperature</b>    | -75°C                                                                                                           |
| <b>Tolerance</b>           | Class 1                                                                                                         |
| <b>Standards Met</b>       | Colour code (cores & jacket) to IEC-584-3                                                                       |



|                |                        |
|----------------|------------------------|
| Connector Type | Plug                   |
| Connector Size | Miniature (moulded-on) |
| Series         | Exposed Junctions      |