


Termopar de unin expuesta ANSI con aislamiento PFA con enchufe moldeado - Tipo K - 3M



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Necesita calibrar su sensor de temperatura?

Trazable a ISO17025 estándares de calibración (UKAS), Labfacility ofrece una opción de calibración trazable de 3 o 5 puntos utilizando nuestra instalación de calibración interna.

Tenga en cuenta que si agrega una opción de calibración a su pedido, se comunicará con usted con respecto a la información de entrega.

Características técnicas**Specifications**

Product Code	XE-0027-001
General Description	Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, gasses, steam etc.
Thermocouple Type	K
Thermocouple Junction	Exposed
Cable Length	3M
Cable Type	PFA Teflon® twin twisted pair
Core / Strands	1/0.3mm
Termination Type	Moulded-on type K ANSI miniature thermocouple plug
Max. Temperature	260°C
Min. Temperature	-75°C
Tolerance	Tolerance Class 1 for optimum accuracy
Standards Met	ANSI MC96.1 Colour Coded