



## Cable / cable termopar tipo J PFA aislado de dos pares trenzados (IEC) - hilo de 1/0,2 mm




**10M**



**TYPE-J**

**50M**



**TYPE-J**

Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Cable / cable de termopar tipo J de par trenzado tipo PFA (IEC)**

Doble par trenzado de tefln PFA para extender o fabricar termopares simples. El teflnPFA tiene una buena resistencia y flexibilidad mecánica, resistente a aceites, cidos y otros fluidos adversos, gases, vapor y presión.

**Especificaciones**
**Specifications**

<b>General Description</b>	Resistant to oils, acids other adverse agents and fluids. Good mechanical strength and flexibility. PTFE better for steam/elevated pressure environments.
<b>Cable Length</b>	10m, 25m, 50m, 100m, 200m
<b>Cable Type</b>	Single pair of PFA insulated conductors twisted together
<b>Core / Strands</b>	1/0.2mm
<b>Conductor Cross Section 1/0.2 (mm<sup>2</sup>)</b>	0.032
<b>+ Colour</b>	Black
<b>- Colour</b>	White
<b>Drain Wire</b>	No
<b>Insulation Material</b>	PFA Teflon®
<b>Loop Resistance 1/0.2 (Ohms per combined metre)</b>	19.3
<b>Max. Temperature</b>	+260°C
<b>Min. Temperature</b>	-75°C
<b>+ Conductor</b>	Iron
<b>- Conductor</b>	Constantan



# LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

<b>Screen</b>	No
<b>Standards Met</b>	Colour code (cores & jacket) to IEC-584-3
<b>Thermocouple Type</b>	J
<b>Tolerance</b>	Class 1