



# LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

## **Termopar con aislamiento mineral con sello de olla liso y cable ANSI aislado con PFA con mini enchufe instalado - Tipo K - 1,5 mm x 250 mm**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Necesita calibrar su sensor de temperatura?**

Trazable a ISO17025 estándares de calibración (UKAS), Labfacility ofrece una opción de calibración trazable de 3 o 5 puntos utilizando nuestra instalación de calibración interna.

**Tenga en cuenta que si agrega una opción de calibración a su pedido, se comunicará con usted con respecto a la información de entrega.**

**Características técnicas****Specifications**

|                              |                                                                                    |
|------------------------------|------------------------------------------------------------------------------------|
| <b>Product Code</b>          | XE-0304-001                                                                        |
| <b>General Description</b>   | Highly flexible, sheath can be bent/formed to suit many applications and processes |
| <b>Thermocouple Type</b>     | K                                                                                  |
| <b>Thermocouple Junction</b> | Insulated hot junction                                                             |
| <b>Probe Diameter</b>        | 1.5mm                                                                              |
| <b>Probe Length</b>          | 250mm                                                                              |
| <b>Sheath Material</b>       | 310 stainless steel sheath                                                         |
| <b>Pot Type</b>              | Plain pot seal (200°C)                                                             |
| <b>Cable Length</b>          | 1m                                                                                 |
| <b>Cable Type</b>            | PFA Teflon® insulated flat pair cable and tails (colour coded to ANSI MC96.1)      |
| <b>Core / Strands</b>        | 7/0.2mm                                                                            |
| <b>Cable Termination</b>     | Bare Tails                                                                         |
| <b>Max. Temperature</b>      | +1100°C                                                                            |
| <b>Standards Met</b>         | Colour coded to ANSI MC96.1                                                        |