

Parche autoadhesivo PT100 Sensor con cubierta exterior aislada de PFA - Tipo PRT - 5M de longitud



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

El estilo RTF4/NAH es un sensor de superficie encapsulado dentro de un parche de goma de silicona.

Se utiliza para aplicaciones de superficie

Tolerancia de clase B

Plomo aislado con PFA

Terminacin de cola de 4 hilos a IEC60751

Opciones de cable PFA de 1, 3 o 5 m disponibles

Caractersticas tcnicas

Specifications

Product Code	XE-3687-001
Sensor Type	Silicone rubber patch with self adhesive foil backing
Element	Pt100
Patch dimensions	L40 x W15mm x D5mm
Cable Length	5M
Cable Type	PFA insulated outer jacket
Core / Strands	7/0.1mm
Cable Termination	Bare Tails
Max. Temperature	+150°C
Min. Temperature	-50°C
Accuracy	Class B
Number of Wires	4
Series	Patch Pt100