



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Termopares con aislamiento mineral de respuesta rápida de 0,5 mm con enchufe IEC en miniatura - Unión aislada - 250 mm



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Termopar con aislamiento mineral de respuesta rápida en tipo K. Varias longitudes disponibles que terminan con un enchufe en miniatura IEC (220 °C) para una conexión rápida y sencilla.

Para las versiones de 0,25 mm, 0,75 mm y 0,81 mm de diámetro, utilice nuestros [formularios de sensores personalizados](#) para enviar sus requisitos

Necesita calibrar su sensor de temperatura?

Trazable a los estándares de calibración ISO17025 (UKAS), Labfacility ofrece la opción de una calibración trazable de 3 o 5 puntos utilizando nuestra instalación de calibración interna, puede seleccionar cualquier punto de temperatura entre -10 °C y +200 °C.

Tenga en cuenta que si agrega una opción de calibración a su pedido, nos pondremos en contacto con usted con respecto a la información de entrega.

Características técnicas

Specifications

Product Code	XE-3206-001
General Description	Highly flexible, sheath can be bent/formed to suit many applications and processes
Sensor Type	Mineral Insulated
Thermocouple Type	K
Element/hot junction	Single element, junction insulated or grounded from sheath
Probe Diameter	0.5mm
Probe Length	250mm
Sheath Material	Stainless steel 310
Termination Type	Miniature flat pin plug, colour coded in accordance IEC 584
Max. Temperature	+750°C. Plug Max. temperature range: 200°C
Min. Temperature	-40°C
Standards Met	IEC 584



Connector Type	Plug
Connector Size	Miniature
Series	Mineral Insulated