


**Termopar de boquilla IEC, cable aislado de fibra  
de vidrio con trenzado de acero inoxidable - Tipo  
K - Terminacin de colas desnudas - 1M**



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Caractersticas tcnicas****Specifications**

|                              |                                                          |
|------------------------------|----------------------------------------------------------|
| <b>Product Code</b>          | XE-0883-001                                              |
| <b>General Description</b>   | Thermocouple housed in a stainless steel threaded bolt   |
| <b>Thermocouple Type</b>     | K                                                        |
| <b>Thermocouple Junction</b> | Grounded hot junction for fast response, M6x1mm thread   |
| <b>Probe Diameter</b>        | 4.5mm                                                    |
| <b>Probe Length</b>          | 150mm                                                    |
| <b>Cable Length</b>          | 1M                                                       |
| <b>Cable Type</b>            | Glassfibre insulated lead with stainless steel overbraid |
| <b>Core / Strands</b>        | 7/0.2mm                                                  |
| <b>Cable Termination</b>     | Bare tails                                               |
| <b>Termination Type</b>      | Grounded hot junction for fast response, M6x1mm thread   |
| <b>Max. Temperature</b>      | +350°C                                                   |
| <b>Min. Temperature</b>      | -60°C                                                    |
| <b>Standards Met</b>         | IEC                                                      |
| <b>Dimensions</b>            | 25x13mm shim (0.2mm thick)                               |
| <b>Thread</b>                | M6 x 1mm thread                                          |