

## Sonda de punta plana Tipo RTD / PRT



[Click here to view product](#)

<b>Product Code</b>	XE-3697
<b>General Description</b>	316 stainless steel probe, 4.0mm diameter (6mm max. across flat area of tip) x 150mm long overall
<b>Sensor Type</b>	Pt100 (100 Ohms @ 0°C) to IEC 751, Class B
<b>Probe Temperature Range</b>	-50°C to +250°C
<b>Cable Length</b>	1m, 2m, 5m
<b>Cable Type</b>	7/0.2mm Teflon® insulated 2 core twisted leads
<b>Termination Type</b>	2-wire tails
<b>Accessories</b>	1/8" BSPP brass male compression fitting with locknut included