

## Panel de aluminio para conector de termopar con enchufes estándar ANSI tipo J - 2 vas



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

**Paneles de conectores estndar de termopar preensamblados**

Un conjunto estndar de panel horizontal preensamblado diseado para usarse con termopares o cables con tapones estndar. Robusto y perfecto para montarse en salas de control, bancadas de pruebas, aplicaciones de laboratorio, salas de control y ms. Admiten cdigos de calibracin como K, J, T con conectores rpidos y pueden acomodar circuitos de 1 a 24 vas, con un rango mximo de temperatura de hasta +120C.

Suministrado previamente equipado con

[vasos estndar de fascia](#)

Circuito bidireccional

Calibracin ANSI tipo J

Temperatura mxima 120C

**Aplicaciones tpicas**

OEMs

Constructores de paneles de instrumentacin

Salas de control

Bancos de pruebas y patines

**Specifications**

|                            |                                                                                          |
|----------------------------|------------------------------------------------------------------------------------------|
| <b>Product Code</b>        | XE-7466-001                                                                              |
| <b>General Description</b> | Accepts standard round pin plug connector. Nylon clip for quick, simple fixing to panel. |
| <b>Thermocouple Type</b>   | J ANSI                                                                                   |
| <b>Number of Ways</b>      | 2 Way                                                                                    |
| <b>Connector Size</b>      | Standard                                                                                 |
| <b>Connector Type</b>      | Fascia Mounting Socket                                                                   |
| <b>Colour</b>              | Black                                                                                    |
| <b>Dimensions</b>          | H66mm x W69mm                                                                            |



|                   |                        |
|-------------------|------------------------|
| Max. Temperature  | 120°C                  |
| +Positive Contact | Iron                   |
| -Negative Contact | Copper Nickel          |
| Standards Met     | BS EN 50212:1997. RoHS |