


## Panel de aluminio para conector de termopar con tomas miniatura JIS tipo K - 8 vas



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

### **Paneles de conectores de termopar miniatura preensamblados**

Un conjunto de panel horizontal en miniatura preensamblado diseñado para usarse con termopares o cables con tapones en miniatura. Robusto y perfecto para montarse en salas de control, bancadas de pruebas, aplicaciones de laboratorio, salas de control y ms. Admiten el código de calibración K con cables de cable rápido y pueden acomodar circuitos de 1-24 vas, con un rango máximo de temperatura de hasta +120C.

Suministrado previamente equipado con

[vasos de fascia miniatura](#)

Circuito de 8 vas

Calibración JIS tipo K

Temperatura máxima 120C

### **Aplicaciones típicas**

OEMs

Constructores de paneles de instrumentación

Salas de control

Bancos de pruebas y patines

## **Specifications**

|                            |                                                                            |
|----------------------------|----------------------------------------------------------------------------|
| <b>Product Code</b>        | XE-7601-001                                                                |
| <b>General Description</b> | All fascia mounting sockets are polarised by means of unequally sized pins |
| <b>Thermocouple Type</b>   | K JIS                                                                      |
| <b>Number of Ways</b>      | 8 Way                                                                      |
| <b>Connector Size</b>      | Miniature                                                                  |
| <b>Connector Type</b>      | Fascia Mounting Socket                                                     |
| <b>Colour</b>              | Blue                                                                       |
| <b>Dimensions</b>          | H45mm x W145mm                                                             |
| <b>Max. Temperature</b>    | 120°C                                                                      |



|                   |                        |
|-------------------|------------------------|
| +Positive Contact | Nickel Chromium        |
| -Negative Contact | Nickel Alloy           |
| Standards Met     | BS EN 50212:1997. RoHS |