



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Termopar de unin expuesta IEC de doble trenza con aislamiento PFA con enchufe en miniatura - Tipo K - Tamao de hebra de 7 / 0.2 - Longitud de 300 mm



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Unin expuesta soldada de respuesta rpida disponible en la especificacin de cable de clase 1 de acuerdo con BS EN 60584-3: 2008 con una terminacin de enchufe en miniatura.

Ideal para aplicaciones de prueba y desarrollo.

Caractersticas tcnicas

Specifications

Product Code	XE-0442-001
General Description	Fast response, welded exposed junction
Sensor Type	Exposed Junction
Thermocouple Type	K IEC
Cable Length	300mm
Cable Type	Teflon® PFA insulated twin-twisted lead
Core / Strands	7/0.2mm
Termination Type	Miniature flat pin plug, colour coded in accordance IEC 584
Max. Temperature	250°C
Min. Temperature	-75°C
Tolerance	Class 1
Standards Met	IEC-584-3
Connector Type	Plug
Connector Size	Miniature
Series	Exposed Junctions