

Termopar de punta soldada expuesta de fibra de vidrio de alta temperatura ANSI tipo K con terminacin de enchufe en miniatura - 10 m de longitud



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Necesita calibrar su sensor de temperatura?

Trazable a ISO17025 estándares de calibración (UKAS), Labfacility ofrece una opción de calibración trazable de 3 o 5 puntos utilizando nuestra instalación de calibración interna.

Tenga en cuenta que si agrega una opción de calibración a su pedido, se comunicará con usted con respecto a la información de entrega.

Características técnicas**Specifications**

Product Code	XE-5645-001
General Description	Fast response, welded exposed junction. Good temperature resistance (not suitable in fluids)
Sensor Type	Exposed Junction
Thermocouple Type	K
Cable Length	10M
Cable Type	high temperature glassfibre insulated twisted cable
Core / Strands	1/0.711mm conductors (21awg)
Cable Termination	Miniature Plug
Max. Temperature	700°C
Min. Temperature	0°C
Tolerance	Tolerance to ANSI MC96.1 Class 2
Standards Met	Colour code to ANSI MC96.1
Connector Type	Plug
Connector Size	Miniature



Colour	Yellow
Series	Exposed Junctions