

## Medidor lser de distancia GT120M



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

El Medidor de Distancia Lser es una herramienta altamente verstil y conveniente diseada para una amplia gama de aplicaciones de la construccin e industria. Proporciona mediciones precisas de distancia, rea y volumen, lo que la convierte en invaluable para los profesionales que necesitan precisin y eficiencia en el lugar.

Ideal para su uso en espacios grandes como habitaciones, apartamentos, edificios, desarrollos inmobiliarios, fbricas, almacenes, jardines, carreteras y proyectos de infraestructura, este dispositivo garantiza resultados fiables y consistentes. Su diseo fcil de usar permite mediciones rpidas y precisas, ayudando a ahorrar tiempo, reducir errores y mejorar la productividad en muchos campos donde los datos precisos de distancia y dimensiones son esenciales.

### Especificaciones

## Specifications

|                                      |                                                                                                                           |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| <b>Product Code</b>                  | XE-4158-001                                                                                                               |
| <b>Model</b>                         | GT120M                                                                                                                    |
| <b>General Description</b>           | Laser Distance Meter with Built-in Spirit Level                                                                           |
| <b>Type</b>                          | Single/Continuous Measurement - Area/Volume/Pythagorean Calculation Measurement                                           |
| <b>Communications Protocol</b>       | Laser: class II, 635nm, <1mW                                                                                              |
| <b>Accuracy</b>                      | +/-2mm / +/-100*10 <sup>-6</sup> *D                                                                                       |
| <b>Readings</b>                      | Data Storage: 30 groups                                                                                                   |
| <b>Storage Temperature Range</b>     | -20°C - 60°C                                                                                                              |
| <b>Ambient Operating Temperature</b> | 0°C - 40°C                                                                                                                |
| <b>Battery</b>                       | 3 x 1.5V AAA                                                                                                              |
| <b>Dimensions</b>                    | 110 x 51.3 x 26.5 mm                                                                                                      |
| <b>Automatic Shutdown</b>            | Automatic laser shutdown: approximately 30 seconds of inactivity. Auto power off: approximately 180 seconds of inactivity |
| <b>Weight</b>                        | 90.2g                                                                                                                     |