


Cable / cable de termopar plano tipo T PFA IEC - hilo 1/0,508 mm



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Cable/cable termopar plano aislado con PFA - Colocado plano, lado a lado y revestido con PFA. Clase de tolerancia
 1

No encuentras lo que necesitas? Llama o enva un correo electronico a nuestro equipo tcnico de ventas al +44 (0) 1243 871 280 o sales@labfacility.com para recibir ayuda con la seleccin de productos y el soporte tcnico

Especificaciones

Specifications

General Description	Resistant to oils, acids other adverse agents and fluids. Good mechanical strength and flexibility. PTFE better for steam/elevated pressure environments.
Cable Length	10m, 25m, 50m, 100m, 200m
Cable Type	PFA insulated, laid flat with PFA jacket
Core / Strands	1/0.508mm
Conductor Cross Section 1/0.508 (mm²)	0.203
Outer Colour	Brown
+ Colour	Brown
- Colour	White
Drain Wire	No
Insulation Material	PFA Insulated
Loop Resistance 1/0.508 (Ohms per combined metre)	2.5
Max. Temperature	260°C
Min. Temperature	-75°C
+ Conductor	Copper



- Conductor	Constantan
Screen	No
Standards Met	Colour code (cores & jacket) to IEC-584-3
Thermocouple Type	T
Tolerance	Class 1