


Cable / cable termopar plano aislado de fibra de vidrio tipo J (IEC) - hilo de 1/0,2 mm



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockings of Thermocouple Cables. The Company has been trading since 1971 and is ISO9001 accredited.

Construccin de pares planos aislados con fibra de vidrio, conductores colocados planos, fibra de vidrio aislada con fibra de vidrio en general, silicona barnicada por todas partes. Buena resistencia a la temperatura pero no adecuada donde hay fluidos presentes.

Especificaciones

Specifications

General Description	Good temperature range but will not prevent ingress of fluids. Fairly flexible but does not provide good mechanical protection.
Cable Length	10m, 25m, 50m, 100m, 200m
Cable Type	Flat pair cable
Core / Strands	7/0.2mm
Conductor Cross Section 7/0.2 (mm²)	0.219
Outer Colour	Black & White
+ Colour	Black
- Colour	White
Drain Wire	No
Insulation Material	Glassfibre insulated
Loop Resistance 7/0.2 (Ohms per combined metre)	2.7
Max. Temperature	+350°C (short periods up to 400°C)
Min. Temperature	-60°C
+ Conductor	Iron
- Conductor	Constantan



LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Screen	No
Standards Met	Colour code (cores & jacket) to IEC-584-3
Thermocouple Type	J
Tolerance	Class 2